



# USB Autofocus Camera Module



8MP Sony IMX179

(SKU:B0197)

QUICK START GUIDE

## SPECS

Camera	
Sensor	1/3.2" IMX179AF
Resolution	8MP 3264H x 2448V
Data Format	MJPEG/YUY2
Frame rate	MJPEG 15fps@3264 x 2448, 30fps@1080P; YUY2 30fps@640x 480
Lens	
Field of View (FOV)	D= 74.6°, H= 64.5°, V= 46.6°
Lens Mount	M6.5
Focusing Range	40mm to infinity
IR Sensitivity	Integral IR filter, visible light only
Functionality and Compatibility	
Auto Controlled Features	Saturation, Contrast, Acutance, White balance, Exposure.
Audio	single microphone (optional dual channel)
System Compatibility	Win7/8/10, Linux, Mac and Android with UVC
Power	
Power Supply	DC5V
Working Current	MAX 350mA
Physical	
Operating Temp.	-4°F~167°F (-20°C~+75°C)
Dimension	36x36mm (Mount compatible with 28x28mm)
Cable Length	3.3ft (1M)

## INTRODUCTION

### • About Arducam

Arducam has been a professional designer and manufacturer of SPI, MIPI, DVP and USB cameras since 2012. We also offer customized turnkey design and manufacturing solution services for customers who want their products to be unique.

### • About this USB Camera

The B0197 is a new member of the Arducam's USB camera family. It's an 8MP, UVC compliant, autofocus (AF) USB 2.0 camera. This AF USB camera is based on the 1/3.2" Sony IMX179 image sensor, and you can read more about its specs in the next chapter. Arducam also provides the sample application that demonstrates some of the features of this camera.

### • About UVC

The B0197 is a UVC-compliant camera. The native UVC drivers of Windows, Linux and Mac shall be compatible with this camera so that it does not require extra drivers to be installed.

### • About Customer Service

If you need our help or want to customize other models of USB cameras, feel free to contact us at support@arducam.com

## QUICK START

### • How to download the program

Download the APP Amcap from the following link <https://www.arducam.com/downloads/app/AMCap.exe>

### NOTE:

1. If used with the Android device, USB Camera APP and connect adapter are needed.
2. For Mac OS, please open the native software facetime and select the video camera "TTQ 8MP Camera".

### • How to connect the camera


Connect the one end of the USB 2.0 cable to the USB 2.0 connector provided on the back of B0197, and connect the other end to the USB 2.0 host controller on the computer.

## How to use the program (Windows demo only)

The Menu bar at the top of the shown image contains few menu items and the current preview resolution and the frame rate are displayed on the bottom bar when the application is running. The following sections describe each of the menu items


### • Menu>Devices

This menu will show the available video devices to host PC. The B0197 named "TTQ 8MP Camera". This camera support capturing audio, so the menu shows the "TTQ Audio Device".





### • Menu>Options

The options menu can be used to select the preview and audio and image parameters supported by this camera.





## How to use the program (Windows demo only)

### - Video Capture Pin



## How to use the program (Windows demo only)

### - Video Capture Filter -> Video Proc Amp/Camera Control



## How to use the program (Windows demo only)

### • Menu > Capture

The capture menu is used to capture the still image and video by using this application. You can also select the related parameters.

NOTE: If you want to get the voice from the microphone, you need to select the option "Capture Audio" before capturing video.

